



CR2B223G



3.25" x 21.25" x 18" (H x W x D)

2-burner 230V electric cooktop designed for portrait or landscape installation, with smooth black ceramic glass surface

Highlights:

- 1800W and 1200W cooking elements ensure faster heating
- Innovative design allows the cooktop to be mounted in portrait or landscape style to accommodate any setup
- Fits popular 20" x 16" counter cutouts

Product Features:

Fits popular cutout size	Designed for built-in installation in 20" x 16" cutouts
Versatile placement	Specially designed to be mounted portrait or landscape style with controls being easy to read and manage in either direction
EuroKera black ceramic glass surface	Easy cleanup and elegant style on a smooth ceramic glass surface
Two heating elements	One 1800W burner and one 1200W burner for fast cooking
230V operation	Professional installation required
Push-to-turn controls	Prevents accidents by requiring a small amount of force to turn on cooktop heat
Residual heat indicator	Indicator will illuminate to warn if some part of the glass surface is too hot to touch
Indicator lights	Operating indicators light up to show which burner is in use
ADA compliant design	Upfront controls and easy-to-operate knobs offer easier accessibility



CR2B223G Specifications:

Overview	
Height of Cabinet	3.25" (8 cm)
Width	21.25" (54 cm)
Depth	18.0" (46 cm)
Cabinet	Black
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	20.0
Voltage/Frequency	230 V AC/60 Hz
Weight	18.0 lbs. (8 kg)
Shipping Weight	20.0 lbs. (9 kg)
Estimated Time to Ship	Next day shipping
Parts & Labor Warranty	1 Year
Electric Cooktop	
Heating Type	Radiant
Surface	Glass
Element Type	Glasstop
Number of Elements	2
controls	Dial
Countertop Cutout Height	3.0" (8 cm)
Countertop Cutout Width	20.0" (51 cm)
Countertop Cutout Depth	16.0" (41 cm)
Element #1 Size	5.5" (14 cm)
Element #1 Wattage	1200.0
Element #2 Size	7.0" (18 cm)
Element #2 Wattage	1800.0

