



GCJ1SS



2.88" x 12" x 20" (H x W x D)

1-burner gas cooktop made in Italy with a sealed dual-burner, cast iron grate, and a 304 grade stainless steel surface

Highlights:

1 sealed dual burner provides optimal heating options in a modern design

304 grade stainless steel surface ensures durability and elegance

Cast iron grate supports heavy pots and pans

Product Features:

304 grade stainless steel surface	Long-lasting durability in a sleek design
Sealed burner	Quality burner by Defendi with cast iron caps ensure lasting durability and easier cleanup
Smooth edge design	Provides added safety and blends cleanly into countertops
Dual-ring burner	A 15,000 BTU total burner and 2,050 BTU inner burner meet a variety of cooking needs
Push-to-turn knobs	Safety feature requires you to turn the knob to the "full-on" position before pushing down, waiting for the ignition, and adjusting to your preferred heating level
Designer knobs	Heavy duty brass and aluminum knobs in a round design and steel finish for a modern look
Conversion kit included	Convert operation from natural gas to LP with the included kit
Cast iron grate in a matte finish	Solid cast iron construction to support heavy cookware
Wok ring included	Removable ring included to safely hold a wok over the flame when cooking on the dual burner



GCJ1SS Specifications:

Overview	
Height of Cabinet	2.88" (7 cm)
Width	12.0" (30 cm)
Depth	20.0" (51 cm)
Cabinet	Stainless Steel
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Amps	1.0
Voltage/Frequency	115 V AC/60 Hz
Weight	13.0 lbs. (6 kg)
Shipping Weight	18.0 lbs. (8 kg)
Parts & Labor Warranty	1 Year
UPC	761101064277
Gas Cooktop	
Ignition	Electric
LP Convertible	Yes
Number of Burners	1
Controls	Dial
Surface	Stainless Steel
Grate Material	Cast iron
Cutout Width	11.25" (29 cm)
Cutout Depth	19.0" (48 cm)
Burner #1 BTU	15300.0

