



SCR1105LH



72.5" x 19.5" x 23.5" (H x W x D)

Commercial beverage merchandiser designed for the display and refrigeration of beverages and sealed food, with 9.9 cu.ft. capacity, SS interior, self-closing door, and a digital thermostat

Highlights:

Commercially listed to NSF-7 standards for use in foodservice establishments

Full display all the way down to the floor

Self-closing door is ideal for busy commercial settings

Product Features:

Commercially listed	ETL-S listed to NSF standards and approved to UL-471 electrical standard for commercial use
Double pane tempered glass door	Heat-safe glass door offers full display all the way down to the floor
Stainless steel interior	Walls are constructed from stainless steel for added durability and easy cleanup
Self-closing door	Door will automatically close when left ajar, preventing items from accidentally being exposed to ambient temperatures
LED lighting	LED lighting on both sides and backlit header panel illuminate the interior for easy viewing
Digital thermostat	Electronic controls for precise temperature management
Large capacity	Generous 9.9 cu.ft. interior provides users with spacious storage
Cantilevered shelving	Adjustable shelving accommodates virtually any size with convenient cantilevered system
7 plastic, perforated shelves	Six adjustable full and one removable half shelf accommodate a variety of sizes inside the 9.9 cu.ft. interior



SCR1105LH Specifications:

Overview	
Height of Cabinet	71.75" (182 cm)
Height to Hinge Cap	72.5" (184 cm)
Width	19.5" (50 cm)
Depth	23.5" (60 cm)
Depth with Handle	26.0" (66 cm)
Depth with door at 90°	41.5" (105 cm)
Capacity	9.9 cu.ft. (280 L)
Defrost Type	Automatic
Door	Glass/SS
Cabinet	Stainless Steel
US Electrical Safety	ETL
Canadian Electrical Safety	ETL-C
Sanitation	ETL-S
Amps	2.6
Voltage/Frequency	115 V AC/60 Hz
Weight	165.0 lbs. (75 kg)
Shipping Weight	175.0 lbs. (79 kg)
Parts & Labor Warranty	1 Year
Compressor Warranty	5 Years
UPC	761101076140
Refrigerator Features	
Door Swing	LHD
Reversible	No
Shelf Type	Plastic
Shelf Qty	7
Adjustable Shelves	Yes
Thermostat Type	Digital
Fan Type	Interior
Refrigerant Type	R290a
Refrigerant Amount	1.58oz.
High Side PSI	245.0
Low Side PSI	130.0
Level Legs Qty	4
Interior Light	Yes
Temperature Range	36°F to 43°F
Dimensions	
Interior Height	57.0" (145 cm)

Interior Width	16.38" (42 cm)
Interior Depth	15.0" (38 cm)
Compressor Step Height	9.0" (23 cm)
Compressor Step Width	16.38" (42 cm)
Compressor Step Depth	9.0" (23 cm)

