



STAINLESS STEEL

TWO COMPARTMENT A.D.A. COMPLIANT WALL MOUNTED SCRUB SINK



SCR-ADA-2

Item #: _____ Qty #: _____
 Model #: _____
 Project #: _____



FEATURES:

- Meets A.D.A. Compliance
- Slanted Front Wall Mount Design
- Coved Corner Bowl Radius
- Fully Enclosed Under Section Conceals Plumbing
- Removable Front Panels
- Supplied with Wall Mounting Bracket
- Includes Two K-6 Drains and Two K-410 Strainer Plate

CONSTRUCTION:

- All TIG welded.
 - Welded areas blended to match adjacent surfaces and polished to an upgraded, medical finish.
- satin finish.

MATERIAL:

- 16 Gauge, Type 304 Stainless Steel

Model #	Length	Width	Bowl Depth	Wt.	Cu. Ft.
SCR-ADA-2	60"	21"	12 1/2"	235 lbs.	31

RECOMMENDED FAUCETS & OPTIONS



K-185/K-186



TA-14



K-187

Model #	Description
K-185	Hands Free Sensor Faucet, A/C Powered w/ Manual Wrist Handle, Rose Spray
K-186	Hands Free Sensor Faucet Battery Powered w/ Manual Wrist Handle, Rose Spray
K-187	Thermostatic Mixing Valve w/ Checks
TA-14	Panel Lock



Customer Service Available To Assist You 1-800-645-3166 8:30 am - 7:00 pm E.S.T.

For Orders & Customer Service:
 Email: customer@advancetabco.com or Fax: 631-242-6900





For Smart Fabrication™ Quotes:
 Email: smartfab@advancetabco.com or Fax: 631-586-2933

DIMENSIONS and SPECIFICATIONS


TOL Overall: ± .500"

ALL DIMENSIONS ARE TYPICAL

SCR-ADA-2



TYPICAL REAR VIEW



WALL MOUNTING CLIP DETAIL

235 lbs.

