

# Solenoid coil BMSFW-120/60-CSA

Part number: 104080

FESTO



## Data sheet

Feature	Value
Type code	BMSFW
Mounting position	Any
Switching position indication	no
Min. pick-up time	10 ms
Duty cycle	100%
Power factor cos {phi}	0.7
Coil characteristics	120 V AC: 60 Hz, initial power 10.0 VA, holding power 8 VA
Permissible frequency fluctuations	+/- 5%
Permissible voltage fluctuations	+/- 10 %
Certification	CSA (OL)
CE marking (see declaration of conformity)	As per EU low voltage directive
Degree of protection	IP65
Ambient temperature	-5 °C ... 40 °C
Max. tightening torque of socket	0.4 Nm
Product weight	55 g
Electrical connection	3-pin Plug flags with connection diagram as per Festo standard for MSSD-F
Type of mounting	With knurled nut
Note on materials	RoHS-compliant
Solenoid coil material	Duroplast Copper Steel
Material of winding	Copper