

Barbed bulkhead connector SCN-PK-4

Part number: 11973

FESTO



Data sheet

Feature	Value
Nominal width	2.8 mm
Type code	SCN
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Ambient temperature	0 °C ... 60 °C
Pneumatic connection 1	For pneumatic tubing outside diameter 6 mm
Note on materials	RoHS-compliant
Housing material	Aluminum
Nut material	Steel, galvanized