


# Pneumatic muffler AMTE-M-LH-M5

Part number: 1205858

FESTO



## Data sheet

Feature	Value
Type code	AMTE
Mounting position	Any
Pack size	20
Symbol	00991473
Operating pressure	0 bar ... 10 bar
Flow rate with respect to atmosphere	255 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Noise level	72 dB(A)
Ambient temperature	-40 °C ... 80 °C
Product weight	1.5 g
Pneumatic connection	M5
Cushioning insert material	Bronze
Material of screwed trunnion	Brass
Note on materials	RoHS-compliant