

# Pneumatic muffler AMTE-M-LH-G14

Part number: 1205861

FESTO



## Data sheet

| Feature                                  | Value                                         |
|------------------------------------------|-----------------------------------------------|
| Type code                                | AMTE                                          |
| Mounting position                        | Any                                           |
| Pack size                                | 20                                            |
| Symbol                                   | 00991473                                      |
| Operating pressure                       | 0 bar ... 10 bar                              |
| Flow rate with respect to atmosphere     | 3140 l/min                                    |
| Operating medium                         | Compressed air as per ISO 8573-1:2010 [7:-:-] |
| Information on operating and pilot media | Operation with oil lubrication possible       |
| Corrosion resistance class (CRC)         | 1 - Low corrosion stress                      |
| Noise level                              | 83 dB(A)                                      |
| Ambient temperature                      | -40 °C ... 80 °C                              |
| Product weight                           | 13 g                                          |
| Pneumatic connection                     | G1/4                                          |
| Cushioning insert material               | Bronze                                        |
| Material of screwed trunnion             | Brass                                         |
| Note on materials                        | RoHS-compliant                                |