

# Parallel kit EAMM-U-60-D32-57A-91-S1

Part number: 1210453

FESTO



## Data sheet

| Feature                | Value                  |
|------------------------|------------------------|
| Size                   | 60                     |
| Type code              | EAMM-U                 |
| Mounting position      | Any                    |
| Gear ratio             | 1:1                    |
| Max. rotational speed  | 6000 1/min             |
| Storage temperature    | -25 °C ... 60 °C       |
| Relative air humidity  | 0 - 95 %               |
| Degree of protection   | IP65                   |
| Ambient temperature    | -10 °C ... 60 °C       |
| Mass moment of inertia | 26.7 kgmm <sup>2</sup> |
| No-load driving torque | 0.07 Nm                |
| Transferable torque    | 3 Nm                   |
| Product weight         | 1190 g                 |
| Note on materials      | RoHS-compliant         |