


Pneumatic muffler AMTC-P-PC10

Part number: 1224460

FESTO



Data sheet

Feature	Value
Type code	AMTC
Mounting position	Any
Pack size	1
Symbol	00991473
Operating pressure	0 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Noise level	58 dB(A)
Ambient temperature	-5 °C ... 60 °C
Product weight	2 g
Pneumatic connection	Cartridge 10 mm
Cushioning insert material	PE
Material of screwed trunnion	PE
Note on materials	RoHS-compliant