

Solenoid coil MSN1W-230AC-OD

Part number: 123062

FESTO



Data sheet

Feature	Value
Type code	MSN1W
Mounting position	Any
Min. pick-up time	10 ms
Duty cycle	100%
Power factor cos {phi}	0.7
Coil characteristics	230 V AC: 50 Hz, initial power 7.5 VA, holding power 5.0 VA 230 V AC: 60 Hz, initial power 5.0 VA, holding power 3.7 VA
Permissible voltage fluctuations	+/- 10 %
Maritime classification	See certificate
CE marking (see declaration of conformity)	As per EU low voltage directive
Temperature of medium	-10 °C ... 50 °C
Degree of protection	IP65
Ambient temperature	-10 °C ... 50 °C
Product weight	80 g
Electrical connection	3-pin Form A as per DIN EN 175301-803
Type of mounting	Clamped With retaining clamp With accessories
Note on materials	Free of copper and PTFE
Housing material	PA
Material of pin contacts	Steel
Material of winding	Copper