

Push-in sleeve QSH-4-100

Part number: 130723

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	2.5 mm
Type code	QSH
Mounting position	Any
Pack size	100
Operating pressure for entire temperature range	-0.95 bar ... 6 bar
Temperature-dependent operating pressure	-0.95 bar ... 14 bar
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7::-] Water as per manufacturer's declaration at www.festo.com
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 80 °C
Product weight	0.5 g
Pneumatic connection 1	Push-in sleeve QS-4
Pneumatic connection 2	Push-in sleeve QS-4
Releasing ring color	Blue
Note on materials	RoHS-compliant
Housing material	PBT