

Push-in L-fitting QSML-M7-4-100

Part number: 130773

FESTO



Data sheet

Feature	Value
Size	Mini
Nominal width	2 mm
Type code	QSML
Type of seal on screwed trunnion	Sealing ring
Mounting position	Any
Pack size	100
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.95 bar ... 6 bar
Temperature-dependent operating pressure	-0.95 bar ... 14 bar
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 80 °C
Nominal tightening torque	3.35 Nm
Tolerance for nominal tightening torque	± 20%
Product weight	5.6 g
Pneumatic connection 1	External thread M7
Pneumatic connection 2	for pneumatic tubing outside diameter 4 mm
Releasing ring color	Blue
Note on materials	RoHS-compliant
Housing material	PBT
Releasing ring material	POM
Material of tubing seal	NBR
Material of tube retaining claw	High-alloy stainless steel