

Bellows gripper DHEB-12-E-U-E-L

Part number: 1320811

FESTO



Data sheet

Feature	Value
Size	12
Stroke of bellows	5.5 mm
Min. diameter to be gripped	13 mm
Max. diameter to be gripped	17 mm
Type code	DHEB
Mounting position	Any
Mode of operation	Single-acting Closed
Structural design	Contracting diaphragm Positively driven motion sequence
Guide	Basic guide
Position sensing	None
Operating pressure	5 bar ... 8 bar
Resetting pressure	<1 bar
Max. operating frequency of pneumatic gripper	≤4 Hz
Min. opening time at 6 bar	20 ms
Min. closing time at 6 bar	40 ms
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	5 °C ... 60 °C
Average replacement interval for the bellows	0.5 MioCyc
Guide value for payload	0.12 kg
Product weight	18 g
Type of mounting	Optionally: With external thread With lock nut
Pneumatic connection	M5
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Bellows material	EPDM
Housing material	Aluminum Anodized