


# Bellows gripper DHEB-14-E-U-S-P

Part number: 1320823

FESTO



## Data sheet

| Feature                                       | Value                                                              |
|-----------------------------------------------|--------------------------------------------------------------------|
| Size                                          | 14                                                                 |
| Stroke of bellows                             | 7 mm                                                               |
| Min. diameter to be gripped                   | 15 mm                                                              |
| Max. diameter to be gripped                   | 19.5 mm                                                            |
| Type code                                     | DHEB                                                               |
| Mounting position                             | Any                                                                |
| Mode of operation                             | Single-acting<br>Closed                                            |
| Structural design                             | Contracting diaphragm<br>Positively driven motion sequence         |
| Guide                                         | Basic guide                                                        |
| Position sensing                              | None                                                               |
| Operating pressure                            | 5 bar ... 8 bar                                                    |
| Resetting pressure                            | <1 bar                                                             |
| Max. operating frequency of pneumatic gripper | ≤4 Hz                                                              |
| Min. opening time at 6 bar                    | 20 ms                                                              |
| Min. closing time at 6 bar                    | 40 ms                                                              |
| Operating medium                              | Compressed air as per ISO 8573-1:2010 [7:4:4]                      |
| Information on operating and pilot media      | Operation with oil lubrication possible (required for further use) |
| Corrosion resistance class (CRC)              | 2 - Moderate corrosion stress                                      |
| For use in the food industry                  | See supplementary material information                             |
| Ambient temperature                           | 5 °C ... 60 °C                                                     |
| Average replacement interval for the bellows  | 1 MioCyc                                                           |
| Guide value for payload                       | 0.15 kg                                                            |
| Product weight                                | 20 g                                                               |
| Type of mounting                              | Optionally:<br>With external thread<br>With lock nut               |
| Pneumatic connection                          | M3                                                                 |
| Note on materials                             | Contains paint-wetting impairment substances<br>RoHS-compliant     |
| Bellows material                              | VMQ (silicone)                                                     |
| Housing material                              | Aluminum<br>Anodized                                               |