

Cartridge QSPK10-4

Part number: 132979

FESTO



Data sheet

Feature	Value
Size	Mini
Nominal width	2.3 mm
Type code	QSPK10
Type of seal on screwed trunnion	O-ring
Mounting position	Any
Pack size	10
Structural design	Push-pull principle
Operating pressure for entire temperature range	-0.95 bar ... 10 bar
Maritime classification	See certificate
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-5 °C ... 60 °C
Product weight	1.4 g
Pneumatic connection 1	Cartridge 10 mm
Pneumatic connection 2	for pneumatic tubing outside diameter 4 mm
Releasing ring color	Blue
Note on materials	RoHS-compliant
Housing material	PA-reinforced
Releasing ring material	POM
Material of tubing seal	NBR
Material of tube retaining claw	High-alloy stainless steel