

Push-in bulkhead connector NPQP-H-Q8-E-FD

Part number: 133102

FESTO



Data sheet

Feature	Value
Size	Standard
Nominal width	4.9 mm
Type code	NPQP
Pack size	1
Structural design	Push-pull principle
Temperature-dependent operating pressure	-0.95 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	4 - Particularly high corrosion stress
For use in the food industry	See supplementary material information
Ambient temperature	-20 °C ... 60 °C
Product weight	14.3 g
Pneumatic connection 1	for pneumatic tubing outside diameter 8 mm
Pneumatic connection 2	for pneumatic tubing outside diameter 8 mm
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Housing material	PP
Nut material	High-alloy stainless steel
Material of tube retaining claw	High-alloy stainless steel