

# Drive shaft EAMB-24-9-15X21-16X20

Part number: 1344642

FESTO



## Data sheet

Feature	Value
Diameter of holder 1	15 mm
Diameter of holder 2	16 mm
Size	80
Nominal length	21 mm
Type code	EAMB
Mounting position	Any
Max. rotational speed	8000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	3.1 kgmm <sup>2</sup>
Transferable torque	29 Nm
Product weight	72 g
Note on materials	RoHS-compliant