

# Clamping sleeve EAMH-86-8-C27.3-P

Part number: 1354100

FESTO



## Data sheet

| Feature                | Value                  |
|------------------------|------------------------|
| Size                   | 86                     |
| Type code              | EAMH                   |
| Mounting position      | Any                    |
| Max. rotational speed  | 5000 1/min             |
| Storage temperature    | -25 °C ... 60 °C       |
| Relative air humidity  | 0 - 95 %               |
| Ambient temperature    | -10 °C ... 60 °C       |
| Mass moment of inertia | 10.3 kgmm <sup>2</sup> |
| Product weight         | 128 g                  |
| Note on materials      | RoHS-compliant         |