

Clamping sleeve EAMH-110-19-C34-P

Part number: 1354106

FESTO



Data sheet

Feature	Value
Size	110
Type code	EAMH
Mounting position	Any
Max. rotational speed	5000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	33.3 kgmm ²
Product weight	230 g
Note on materials	RoHS-compliant