

# Clamping sleeve EAMH-145-25-C34-P

Part number: 1354110

FESTO



## Data sheet

Feature	Value
Size	145
Type code	EAMH
Mounting position	Any
Max. rotational speed	4000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	32.1 kgmm <sup>2</sup>
Product weight	217 g
Note on materials	RoHS-compliant