

Counter bearing EAMG-U1-50

Part number: 1354281

FESTO



Data sheet

Feature	Value
Size	50
Type code	EAMG
Mounting position	Any
Max. rotational speed	6000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C ... 60 °C
Product weight	20 g
Note on materials	RoHS-compliant