


# Rotary actuator DSM-16-270-HD-A-B

Part number: 1369111

FESTO



## Data sheet

Feature	Value
Size	16
Swivel angle	0 deg ... 270 deg
Type code	DSM
Mounting position	Any
Mode of operation	Double-acting
Structural design	Rotary vane
Position sensing	For proximity sensor
Symbol	00991265
Operating pressure	3 bar ... 10 bar
Max. swivel frequency at 6 bar	1.5 Hz
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:]
Corrosion resistance class (CRC)	0 - No corrosion stress
Ambient temperature	-10 °C ... 60 °C
Max. axial force	290 N
Max. radial force	300 N
Theoretical torque at 6 bar	2.5 Nm
Product weight	625 g
Type of mounting	With internal thread
Pneumatic connection	M5
Note on materials	Free of copper and PTFE RoHS-compliant
Drive shaft material	Steel Nickel-plated
Seals material	TPE-U(PU)
Housing material	Wrought aluminum alloy