

# Multi-tube connector KM-22-B

Part number: 13694

FESTO



## Data sheet

Feature	Value
Nominal width	4 mm
Type code	KM
Operating pressure	-0.95 bar ... 8 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Max. connections	22
Pneumatic connection	PK-2 PK-3 PK-4