

Quick coupling
EAMD-32-32-14-16X20
Part number: 1377840

FESTO



Data sheet

Feature	Value
Diameter of holder 1	14 mm
Diameter of holder 2	16 mm
Size	32
Nominal length	32 mm
Type code	EAMD
Mounting position	Any
Max. rotational speed	8000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-25 °C ... 60 °C
Mass moment of inertia	14.5 kgmm ²
Transferable torque	12.5 Nm
Product weight	124 g
Note on materials	RoHS-compliant