

Vacuum suction cup VASB-100-1/4-SI-B

Part number: 1382277

FESTO



Data sheet

Feature	Value
Suction cup height compensation	15.5 mm
Nominal width	4 mm
Suction cup diameter	100 mm
Suction cup volume	128 cm ³
Type code	VASB
Connection position	Top
Mounting position	Any
Symbol	00991485
Suction cup shape	Round bellows, 1.5 convolutions
Operating pressure	-0.95 bar ... 0 bar
Nominal operating pressure	-0.7 bar
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
For use in the food industry	See supplementary material information
Ambient temperature	-40 °C ... 200 °C
Holding force at nominal operating pressure	395 N
Product weight	132 g
Type of mounting	Via vacuum connection
Vacuum connection	G1/4
Color	Transparent
Shore hardness	60 +/- 5
Material of screwed trunnion	Wrought aluminum alloy
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Suction cup material	VMQ (silicone)