


Vacuum suction cup VASB-125-3/8-PUR-B

Part number: 1396067

FESTO



Data sheet

Feature	Value
Suction cup height compensation	25 mm
Nominal width	7 mm
Suction cup diameter	125 mm
Suction cup volume	307 cm ³
Effective suction cup diameter	101.8 mm
Type code	VASB
Connection position	Top
Mounting position	Any
Symbol	00991485
Suction cup shape	Round bellows, 1.5 convolutions
Operating pressure	-0.95 bar ... 0 bar
Nominal operating pressure	-0.7 bar
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7:::]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-20 °C ... 60 °C
Holding force at nominal operating pressure	570 N
Product weight	294 g
Type of mounting	Via vacuum connection
Vacuum connection	G3/8
Color	Blue
Shore hardness	60 +/- 5
Material of screwed trunnion	Die-cast zinc
Note on materials	RoHS-compliant
Suction cup material	PUR