

# Vacuum suction cup VAS-30-1/8-PUR-B

Part number: 1396090

FESTO



## Data sheet

Feature	Value
Suction cup height compensation	1.9 mm
Nominal width	3 mm
Suction cup diameter	30 mm
Suction cup volume	1.29 cm <sup>3</sup>
Effective suction cup diameter	24.8 mm
Type code	VAS
Connection position	Top
Mounting position	Any
Symbol	00991485
Suction cup shape	Round, flat
Operating pressure	-0.95 bar ... 0 bar
Nominal operating pressure	-0.7 bar
Operating medium	Atmospheric air based on ISO 8573-1:2010 [7::-]
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-20 °C ... 60 °C
Holding force at nominal operating pressure	34 N
Product weight	12 g
Type of mounting	Via vacuum connection
Vacuum connection	G1/8
Color	Blue
Shore hardness	60 +/- 5
Material of screwed trunnion	Brass
Note on materials	RoHS-compliant
Suction cup material	PUR