

End plate kit NEV-1DA/DB-NPT

Part number: 13996

FESTO



Data sheet

Feature	Value
Width	110 mm
Type code	NEV
Operating pressure	0 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Sub-base mounting type	With through-hole
Pneumatic valve mounting type	Screw-in
Pneumatic connection 1	NPT3/8-18
Pneumatic connection 3	NPT3/8-18
Pneumatic connection 5	NPT3/8-18