


Motor cable NEBM-S1W15-E-5-Q7-LE6

Part number: 1450945

FESTO



Data sheet

Feature	Value
Type code	NEBM
Cable designation	Without label holder
Electrical connection 1, function	Field device end
Electrical connection 1, design	Rectangular
Electrical connection 1, connection type	Socket
Electrical connection 1, cable outlet	Angled
Electrical connection 1, connection technology	Sub-D
Electrical connection 1, number of pins/wires	15
Electrical connection 1, occupied pins/wires	10
Electrical connection for input 1, connection pattern	00995640
Electrical connection 2, function	Control side
Electrical connection 2, connection type	Cable
Electrical connection 2, connection technology	Open end
Electrical connection 2, number of pins/wires	6
Electrical connection 2, occupied pins/wires	6
DC operating voltage range	0 V ... 72 V
Nominal operating voltage DC	24 V
Cable length	5 m
Cable characteristic	Suitable for energy chains
Bending radius, flexible cable installation	≥80 mm
Cable diameter	8 mm
Cable design	6 x 0.75 mm ² Shielded
Nominal conductor cross section	0.75 mm ²
Wire ends	Cable end sleeve
Degree of protection	IP65
Note on degree of protection	In mounted state
Ambient temperature	-40 °C ... 80 °C
Ambient temperature with flexible cable installation	-5 °C ... 80 °C
CE marking (see declaration of conformity)	As per EU RoHS directive
Note on materials	RoHS-compliant
Corrosion resistance class (CRC)	0 - No corrosion stress
Material of cable sheath	TPE-U(PUR)
Color cable sheath	Gray