

# Axial kit EAMM-A-N48-60H

Part number: 1456618

FESTO



## Data sheet

Feature	Value
Type code	EAMM-A
Mounting position	Any
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Degree of protection	IP40
Ambient temperature	-10 °C ... 60 °C
Transferable torque	12.5 Nm
Product weight	470 g
Interface code, actuator	N48
Interface code, motor in	60H
Note on materials	RoHS-compliant