

Clamping sleeve EAMH-86-14-C27.3-P

Part number: 1459337

FESTO



Data sheet

Feature	Value
Size	86
Type code	EAMH
Mounting position	Any
Max. rotational speed	5000 1/min
Storage temperature	-25 °C ... 60 °C
Relative air humidity	0 - 95 %
Ambient temperature	-10 °C ... 60 °C
Mass moment of inertia	8.74 kgmm ²
Product weight	103 g
Note on materials	RoHS-compliant