


Intermediate position module DADM-EP-G6-16

Part number: 1478121

FESTO



Data sheet

Feature	Value
Size	16
Type code	DADM
Mounting position	Any
Structural design	Positively driven motion sequence
Position sensing	For proximity sensor
Symbol	00991270
Operating pressure	3 bar ... 6 bar
Max. impact velocity	0.8 m/s
Maximum pivot time	150 ms
Repetition accuracy	±0.02 mm
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	0 °C ... 60 °C
Max. stop force	1100 N
Product weight	340 g
Type of mounting	Via through-hole and centering sleeve
Pneumatic connection	M5
Note on materials	RoHS-compliant
Seals material	PU
Housing material	Wrought aluminum alloy
Lever material	High-alloy stainless steel