


Hand slide valve VBOH-32-G38

Part number: 1482679

FESTO



Data sheet

Feature	Value
Type code	VBOH
Valve function	3/2, bistable
Pneumatic connection 1	G3/8
Pneumatic connection 2	G3/8
Actuation type	Manual
Type of mounting	Line installation Screw-in
Standard nominal flow rate	220 l/min
Nominal width	9.9 mm
Operating pressure	-0.95 bar ... 12 bar
Ambient temperature	-10 °C ... 80 °C
Housing material	Wrought aluminum alloy Anodized
Operating medium	Compressed air as per ISO 8573-1:2010 [7:4:4]
Width dimension	39.5 mm
Sealing principle	Soft
Mounting position	Any
Structural design	Sleeve gate valve
Type of control	Direct
Symbol	00991286
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Temperature of medium	-10 °C ... 80 °C
Actuating force	41 N
Product weight	70 g
Material of screwed trunnion	Wrought aluminum alloy Anodized
Note on materials	RoHS-compliant
Seals material	NBR