

Bellows kit EADB-V2-63-S10-100

Part number: 1488361

FESTO



Data sheet

Feature	Value
Outside diameter	93 mm
Size	63
Stroke range	10 mm ... 100 mm
Piston rod extension	43 mm
Type code	EADB
Design	Round
Mounting position	Any
Structural design	Bellows kit with ducted exhaust air
Corrosion resistance class (CRC)	3 - High corrosion stress
Media resistance	Stäube Chips Oils Grease Petrol
Degree of protection	IP65 as per IEC 60529
Ambient temperature	-10 °C ... 80 °C
Moving mass	79 g
Product weight	203 g
Type of mounting	Push-on With threaded pin
Pneumatic connection	G1/4
Note on materials	RoHS-compliant
Adaption parts material	Wrought aluminum alloy Anodized
Seals material	NBR
Bellows material	NBR
Threaded pin material	High-alloy stainless steel