


# Air solenoid valve

## VZWD-L-M22C-M-G14-25-V-3AP4-8

FESTO

Part number: 1491987



### Data sheet

Feature	Value
Type code	VZWD
Structural design	Directly controlled poppet valve
Actuation type	Electrical
Sealing principle	Soft
Mounting position	Any
Type of mounting	Line installation
Fitting connection	G1/4
Electrical connection	Form A Plug as per EN 175301-803 Rectangular design
Nominal width	2.5 mm
Valve function	2/2, closed, monostable
Manual override	None
Flow direction	Non-reversible
Medium	Compressed air as per ISO 8573-1:2010 [7:4:4] Inert gas Mineral oil Water Neutral liquids Other flow media on request
Nominal pressure of fitting PN	50
Differential pressure	0 bar
Coil characteristics	230 V AC: 50/60 Hz, initial power 10.5 VA, holding power 7.6 VA
Insulation class	F
Permissible voltage fluctuations	+/- 10 %
Duty cycle	100%
Reset method	Mechanical spring
Type of control	Direct
Symbol	00992979
Medium pressure	0 bar ... 8 bar
Max. viscosity	22 mm <sup>2</sup> /s
Temperature of medium	-10 °C ... 80 °C

<b>Feature</b>	<b>Value</b>
Ambient temperature	-10 °C ... 35 °C
Leak rate to EN 12266-1	A
Flow rate Kv	0.16 m <sup>3</sup> /h
Standard nominal flow rate	170 l/min
On switching time	25 ms
Switching time off	10 ms
Note on materials	Contains paint-wetting impairment substances RoHS-compliant
Housing material	Brass
Material number of housing	CW614N
Seals material	FPM
Product weight	350 g
CE marking (see declaration of conformity)	As per EU low voltage directive
Degree of protection	IP65
Corrosion resistance class (CRC)	1 - Low corrosion stress