

Illuminating seal MEB-LD-230AC

Part number: 151718

FESTO



Data sheet

Feature	Value
Type code	MEB-LD
Switching position indication	LED
Type of mounting	On air solenoid valve with M2.5 central screw
Product weight	0.6 g
Electrical connection	Form C as per DIN EN 175301-803 Rectangular design MSEB
Nominal operating voltage AC	230 V
Surge resistance	2.5 kV
Protective earth connection	Available
Nominal power luminous seal	0.33 W
Permissible voltage fluctuations	+/- 10 %
Degree of protection	IP65
Ambient temperature	-25 °C ... 85 °C
CE marking (see declaration of conformity)	As per EU low voltage directive
Contamination level	3
Housing material	TPE-U(PU)