

Quick coupling socket KD1-M3-A

Part number: 151995

FESTO



Data sheet

Feature	Value
Nominal width	1.5 mm
Type code	KD1
Operating pressure for entire temperature range	-0.95 bar ... 12 bar
Standard nominal flow rate	44 l/min
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	-10 °C ... 60 °C
Nominal tightening torque	0.6 Nm
Tolerance for nominal tightening torque	± 10%
Product weight	2.9 g
Pneumatic connection 1	External thread M3