

# Multi-plug KSV6-12

Part number: 152507

FESTO



## Data sheet

Feature	Value
Nominal width	6 mm
Type code	KSV6
Operating pressure	-0.95 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Max. connections	12
Pneumatic connection	PK-6
Color	Gray
Note on materials	RoHS-compliant