

**Multi-plug
KSV6-22**
Part number: 152508

FESTO



Data sheet

Feature	Value
Nominal width	6 mm
Type code	KSV6
Operating pressure	-0.95 bar ... 10 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Max. connections	22
Pneumatic connection	PK-6
Color	Gray
Note on materials	RoHS-compliant