

# Push-in connector, self-sealing QSK-4

Part number: 153439

**FESTO**



## Data sheet

| Feature                                         | Value                                                                                                                                                             |
|-------------------------------------------------|-------------------------------------------------------------------------------------------------------------------------------------------------------------------|
| Size                                            | Standard                                                                                                                                                          |
| Nominal width                                   | 1.6 mm                                                                                                                                                            |
| Approved tubing type                            | PAN-<br>PAN-MF-<br>PAN-R-<br>PAN-VO-<br>PEN-<br>PFAN-<br>PLN-<br>PTFEN-<br>PUN-<br>PUN-CM-<br>PUN-DUO-<br>PUN-H-<br>PUN-H-DUO-<br>PUN-S-<br>PUN-S-DUO-<br>PUN-VO- |
| Tubing insertion depth                          | 11.5 mm                                                                                                                                                           |
| Type code                                       | QSK                                                                                                                                                               |
| Mounting position                               | Any                                                                                                                                                               |
| Pack size                                       | 1                                                                                                                                                                 |
| Structural design                               | Push-pull principle                                                                                                                                               |
| Operating pressure for entire temperature range | -0.95 bar ... 6 bar                                                                                                                                               |
| Temperature-dependent operating pressure        | -0.95 bar ... 14 bar                                                                                                                                              |
| Maritime classification                         | See certificate                                                                                                                                                   |
| Operating medium                                | Compressed air as per ISO 8573-1:2010 [7:-:-]                                                                                                                     |
| Information on operating and pilot media        | Operation with oil lubrication possible                                                                                                                           |
| Corrosion resistance class (CRC)                | 1 - Low corrosion stress                                                                                                                                          |
| Ambient temperature                             | -10 °C ... 80 °C                                                                                                                                                  |
| Product weight                                  | 3.5 g                                                                                                                                                             |
| Pneumatic connection 1                          | for pneumatic tubing outside diameter 4 mm                                                                                                                        |
| Pneumatic connection 2                          | for pneumatic tubing outside diameter 4 mm                                                                                                                        |
| Releasing ring color                            | Blue                                                                                                                                                              |
| Note on materials                               | RoHS-compliant                                                                                                                                                    |
| Housing material                                | PBT                                                                                                                                                               |
| Releasing ring material                         | POM                                                                                                                                                               |
| Material of tubing seal                         | NBR                                                                                                                                                               |
| Material of tube retaining claw                 | High-alloy stainless steel                                                                                                                                        |