

Ball valve
QH-QS-6
Part number: 153484

FESTO



Data sheet

Feature	Value
Type code	QH
Valve function	2/2 bistable
Pneumatic connection 1	QS-6
Pneumatic connection 2	QS-6
Actuation type	Manual
Type of mounting	Line installation
Standard nominal flow rate	533 l/min
Nominal width	4 mm
Operating pressure	-1 bar ... 10 bar
Ambient temperature	0 °C ... 60 °C
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Sealing principle	Soft
Structural design	Ball valve

Feature	Value
Symbol	00991458
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Product weight	12.5 g
Note on materials	RoHS-compliant