

Barb tubing fitting N-3/4-P-19-MS

Part number: 15638

FESTO



Data sheet

Feature	Value
Nominal width	16.5 mm
Type code	N
Type of seal on screwed trunnion	Sealing ring
Operating pressure for entire temperature range	-0.95 bar ... 16 bar
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Corrosion resistance class (CRC)	1 - Low corrosion stress
Pneumatic connection 1	External thread G3/4
Pneumatic connection 2	For tubing I.D. 19 mm
Note on materials	RoHS-compliant