

Clevis flange SUA-40

Part number: 157323

FESTO



Data sheet

Feature	Value
Size	40
Type code	SUA
Mounting position	Any
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-40 °C ... 90 °C
Product weight	199 g
Note on materials	Free of copper and PTFE RoHS-compliant
Mounting material	Wrought aluminum alloy
Bolt material	Steel, galvanized
Sleeve material	Spring steel
Material of bearing	Polymer
Material of screws	Steel, galvanized
Fuse material	Spring steel
Shaft material	Steel With protective coating