


Round cylinder EG-6-25-PK-3

Part number: 15895

FESTO



Data sheet

Feature	Value
Stroke	25 mm
Piston diameter	6 mm
Type code	EG
Cushioning	At one end Not adjustable
Mounting position	Any
Structural design	Piston Piston rod Cylinder barrel
Position sensing	None
Symbol	00991200
Variants	Piston rod at one end
Operating pressure	3 bar ... 7 bar
Mode of operation	Single-acting Pushing
Operating medium	Compressed air as per ISO 8573-1:2010 [7:-:-]
Corrosion resistance class (CRC)	1 - Low corrosion stress
Ambient temperature	5 °C ... 60 °C
Theoretical force at 6 bar, advancing	11.8 N
Theoretical min. spring return force	2.5 N
Theoretical max. spring return force	5.2 N
Product weight	24 g
Type of mounting	With lock nut
Pneumatic connection	PK-3
Note on materials	RoHS-compliant
Cover material	High-alloy steel
Seals material	NBR
Piston rod material	High-alloy stainless steel
Material of cylinder barrel	High-alloy stainless steel