

Multi-position kit DPVU-32

Part number: 161197

FESTO



Data sheet

| Feature | Value |
|----------------------------------|---|
| Size | 32 |
| Type code | DPVU |
| Corrosion resistance class (CRC) | 2 - Moderate corrosion stress |
| Ambient temperature | -40 °C ... 150 °C |
| Product weight | 111 g |
| Note on materials | Free of copper and PTFE RoHS-compliant |
| Material of flange | Wrought aluminum alloy |
| Material of screws | Steel Galvanized |
| Cylindrical pin material | Steel Galvanized |