

Multi-position kit DPVU-40

Part number: 161198

FESTO



Data sheet

Feature	Value
Size	40
Type code	DPVU
Corrosion resistance class (CRC)	2 - Moderate corrosion stress
Ambient temperature	-40 °C ... 150 °C
Product weight	155 g
Note on materials	Free of copper and PTFE RoHS-compliant
Material of flange	Wrought aluminum alloy
Material of screws	Steel Galvanized
Cylindrical pin material	Steel Galvanized