


# Air solenoid valve MN1H-2-1 1/2-MS-NPT

FESTO

Part number: 161735



## Data sheet

Feature	Value
Type code	MN1H
Structural design	Diaphragm valve
Sealing principle	Soft
Mounting position	Any
Type of mounting	Line installation
Fitting connection	1 1/2 NPT
Nominal width	40 mm
Valve function	2/2, closed, monostable
Manual override	Detenting via accessory Non-detenting
Flow direction	Non-reversible
Medium	Filtered compressed air, 200 µm filter mesh
Exhaust air function	Without flow control option
Reset method	Pneumatic spring
Type of control	Pilot-controlled
Symbol	00991399
Medium pressure	0.5 bar ... 10 bar
Information on operating and pilot media	Operation with oil lubrication possible (required for further use)
Temperature of medium	-10 °C ... 60 °C
Ambient temperature	-10 °C ... 60 °C
Material of screws	High-alloy stainless steel
Material number of screw	1.4301
Product weight	2600 g
Degree of protection	IP65