

# Angled plug socket PEV-1/4-WD-LED-24

FESTO

Part number: 164274



## Data sheet

Feature	Value
Type code	PEV
Certification	RCM compliance mark
Switching status indication	LED yellow
Type of mounting	With through-hole
Electrical connection	4-pin Socket, angled
DC operating voltage range	15 V ... 30 V
Current rating	8 A
Degree of protection	IP65
Ambient temperature	-40 °C ... 90 °C
CE marking (see declaration of conformity)	As per EU EMC directive
Note on materials	RoHS-compliant