

Fiber-optic cable SOEZ-LLG-SE-0,5-M4

Part number: 165357

FESTO



Data sheet

Feature	Value
Type code	SOEZ-LLG
Method of measurement	Through-beam sensor Fiber-optic cable
Ambient temperature	-20 °C ... 160 °C
Size	M4
Product weight	46 g
Housing material	Brass Chrome-plated
Setting range, upper limit	280 mm
Ambient temperature of flexible installation	-20 °C ... 120 °C
Degree of protection	IP54